



REUSEABLE DEPENDABLE



PMA CERTIFICATION VOID WITHOUT THIS INSTRUCTION CARD

(6) RG-67193 FAA-PMA FOR:

LYCOMING, ENGINE MODELS:

IO-360, VO-435, GO-435, GO-480, IO-540, VO-540
TIVO-540, IO-720

INSTALLATION AND MAINTENANCE

1. ALL SURFACES MUST BE CLEAN AND DRY, NO LUBRICANTS OR THREADLOCK (LOCKTITE) TO BE USED.
2. INSTALL GASKET TO VALUE LISTED: LOG NO. 802070481 QTY. 6 POUNDS POUNDS
3. PERFORM TIGHTENING FOR LEAKS, CURE DATE 1Q2005
4. IF THE GASKET BEGINS TO WORSER. REMOVE THIS GASKET AND REINSTALL IN BETTER CONDITION. IF IT IS STILL SERVICEABLE, WASH THOROUGHLY IN HOT SOAP AND WATER, DRY OFF AND REINSTALL.
5. TO REUSE THE GASKET, CLEAN AS DESCRIBED IN # (4) ABOVE

ROBINSON HELICOPTER COMPANY
 P/N RG-67193
 LOG NO. 802070481
 QTY. 6
 CURE DATE 1Q2005

THE GASKET SURFACES MUST BE CLEAN AND DRY

"CAUTION" DO NOT OVER TIGHTEN

REPORT ALL SERVICE DIFFICULTIES PERTAINING TO THIS PRODUCT TO:

REAL GASKETS TENNESSEE 800-635-7325 423-543-6194
2506 Stateline Road, Elizabethton, TN 37643 U.S.A.

Fax 423-543-9772

e-mail chris@realgaskets.com

www.realgaskets.com